




Radiall 狐

2 WAYS POWER DIVIDER 2 - 26.5GHZ

PAGE 1/2 ISSUE 22-09-16A SERIES PART NUMBER R434812001 SPLITTER







All dimensions are in mm.

Weight Specification **35,9880** g







2 WAYS POWER DIVIDER 2 - 26.5GHZ

| PAGE 2/2 | ISSUE 22-09-16A | SERIES SPLITTER | PART NUMBER R434812001 |
|-----------------|------------------------|---------------------------|-------------------------------|
|-----------------|------------------------|---------------------------|-------------------------------|

ELECTICAL CHARACTERISTICS

| Frequency range : | 2 – 26.5 GHz |
|-------------------|--------------|
| Number of ways | 2 |
| Phase | 0° |
| VSWR | |
| Input | 1.6 |
| Output | 1.6 |
| Impedance | 50 Ohms |
| Insertion loss | 1.2 dB max |
| Isolation | 17 dB mini |
| Amplitude balance | ± 0.4 dB |
| Phase Balance | ± 6° |
| Average Power | |
| VSWR load < 1.2 | 10W |
| VSWR load : inf | 1W |

MECHANICAL CHARACTERISTICS

| Connectors : | |
|--------------|---------------|
| Input | SMA3.5 female |
| Output | SMA3.5 female |
| Body | Aluminium |
| Finish | Blue Paint |

ENVIRONMENTAL CHARACTERISTICS

| Operating temperature | -40 / +85 °C |
|-----------------------|---------------|
| Storage temperature | -55 / +125 °C |