



Electrical specifications

Center Frequency (CF): 225 MHz
Pass Band: 210 – 240 MHz
Insertion Loss (CF): 2.00 dB Max
Return Loss: 14 dB Min
Rejection @ 170 - 190 MHz: 30 dB Min
Rejection @ 50 - 150 MHz: 60 dB Min
Rejection @ 260 – 280 MHz: 30 dB Min
Rejection @ 300 - 1000 MHz: 75 dB Min

Impedance: 50 Ohm
CW Power: 200 W

Mechanical

Connector Type: N (F)
Dimensions: 4.00 x 1.00 x 1.00 inches

Environmental

Operating Temperature: -45 to +85° C
Storage Temperature: -55 to +95° C

Shock: 20 G, for 11 msec
Vibration: 20 G, 5 to 200 Hz

Outline Drawing:

