



6500 MHz Suspended Stripline Low Pass Filter

Part Number: AE6500SSL1024



Electrical Specifications

Cut Off Frequency: 6.5GHz
Pass Band Frequency: DC~6.5GHz
Pass Band Insertion Loss:
≤1.0dB @ DC~6.4GHz
≤1.5dB @ 6.4~6.5GHz
Pass Band VSWR: ≤1.3:1
Stop Band Attenuation: ≥60dB @ 7.27~15.3GHz
Impedance: 50 Ohms
Power Handling: ≤15W

Mechanical

Mounting Method: Through Holes
Connector Type: SMA-Female
Dimensions: 31 x 23 x 10 mm

Environmental

Operating Temperature: -45° to +85° C
Storage Temperature: -55° to +95° C
Shock: 20 G. 11ms
Vibration: 20 G. 5 to 200 Hz

Outline Drawing:

