



Electrical specifications

Center Frequency: 25500 MHz
Bandwidth: 21000-30000 MHz
Insertion Loss: 1.0 dB Max
Rejection: 50 dB min @ 14000 MHz
Rejection: 20 dB min @ 33000 MHz
VSWR: 2.0
Impedance: 50 Ω
Power Handling: 5W (CW)

Size Tolerance: As Below (+/- 0.3m)

Mechanical

Connector Type: SMA Female
Mounting: Thru Hole
Dimensions With Mounting: 1.23 x 0.51 x 0.32 in

Environmental

Operating Temperature: -45 to +85° C
Storage Temperature: -55 to +95° C

Outline Drawing:

