



5755-5795 MHz Cavity Bandpass Filter

ANATECH ELECTRONICS INC
RF & Microwave Filters & Products

Part Number: AB5775B785



Electrical specifications

Passband: 5755-5795 MHz
Rejection 1: 20 dB@5740 MHz
Rejection 2: 20 dB@5812 MHz
Group delay variation: 0.75 dB over PB
Power: 1 Watt

Mechanical

Mounting Method: Threaded Mounting Holes
Connector Type: N Female / N male
Dimensions: 3.50" X 3.50" X 1.50" in

Environmental

Operating Temperature: -45 to +85° C
Storage Temperature: -55 to +95° C
Shock: 20 G. 11ms
Vibration: 20 G. 5 to 200 MHz

Outline Drawing:

