



Electrical Specifications

Passband: DC - 520 MHz
Insertion Loss in Passband: 1.0 dB Max
Rejection: >15 dB @ 650 MHz
>50 dB @ 910-3000 MHz

Mechanical

Connector Type: F-Type (F)
Dimensions: 4.0 x 1.25 x 0.75 Inches

Environmental

Operating Temperature: -45 to +85° C
Storage Temperature: -55 to +95° C

Outline Drawing:

