



Electrical specifications

Passband: 495-945MHz
Passband Insertion Loss: <10dB
Passband Return Loss: >14dB
Rejection: 60 dB @ 290 MHz
Rejection 2: 60 dB @ 1150 MHz
Power Handling: 0 dBm
Group Delay: Fo +/- 200 MHz: delay variation 1nS
Input / Output Impedance: 50 Ohms

Mechanical

Connector Type: SMA (F)
Dimensions: 3.75 x 1 x .5 inches

Environmental

Operating Temperature: -40 to +85 deg.C
Storage temperature: -65 to +95 deg.C
Shock: 20 G's, 1/2 sine, 11ms
Vibration: 10 G's, 10-2000Hz
Relative Humidity: 0-95%

Outline Drawing:

