



## Summary

[Request a quote](#)

[Catalog](#)

Coax	1
Plug	Plug - Straight
Locking system	Push-pull
Jacket cable outside diameter [mm]	2.80 - 3.10 mm
Matching parts	<a href="#">ERA.00.250.CLL</a>
Series	00 - NIM-CAMAC

## Technical details

[https://www.lemo.com/int\\_en/solutions/specialties/00-nim-camac/ffa-00-250-clac31.html](https://www.lemo.com/int_en/solutions/specialties/00-nim-camac/ffa-00-250-clac31.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

## Electrical Configuration

Coax	1
Contact Termination Coax	Solder
R (max)	6.1 mOhm
Insert configuration value	0.25 - 1 Coax (50 Ohm)
Insulator	L: PEEK (UL 94 / V-0/1.5)
Rated current	4 Amps
Impedance	50 Ohm
VSWR	1.09 + 0.11 * f/GHz
Vtest	2100 V (AC), 3000 V (DC)
Contact Type	Coaxial 50 Ohm (Solder)
Test voltage	2.1 kV (rms)
Cable type	RG 174 A/U
Bucket Dia.	0.6 mm (0.024in)
Contact Dia.	0.7 mm (0.028in)

## Form & Material

Shell style / Model id	FFA - Straight plug with cable collet
Plug	Straight
Housing material	Brass (chrome plated [SAE AMS 2460]) shell and collet nut, nickel plated [SAE AMS QQ N 290] brass latch sleeve and mid pieces
Locking system	Push-pull
Keying	Circular, male
Weight	2.74 g

## Environment

Environmental protection	IP50
Minimal temperature	-55°C / +250°C
F ret (min)	100 N
Salt Spray Corrosion	>1000 hr

[https://www.lemo.com/int\\_en/solutions/specialties/00-nim-camac/ffa-00-250-clac31.html](https://www.lemo.com/int_en/solutions/specialties/00-nim-camac/ffa-00-250-clac31.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

## Cable fixation

Cable termination protection	Standard back nut (no additional protection)
Fixation type	Cable collet
Jacket cable outside diameter [mm]	2.80 - 3.10 mm



# Recommended By Lemo

## Accessories

### Tools

Spanner wrench	<a href="#">DCD.00.ZZZ.PA045</a>
----------------	----------------------------------

# Cables

Cable PartNumber	Material	Colour	Cable image
17420	PVC	Black	
31600	PTFE	Brown	
CCX.50.RG1.74AU28N	PVC	Black	
CCX.50.RG1.74AU28N	PVC	Black	
CCX.50.RG3.16U28M	PTFE	Brown	

[https://www.lemo.com/int\\_en/solutions/specialties/00-nim-camac/ffa-00-250-clac31.html](https://www.lemo.com/int_en/solutions/specialties/00-nim-camac/ffa-00-250-clac31.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.