



REVISIONS					
REV.	DESCRIPTION	DATE	APPROVED		
Α	INITIAL RELEASE	04/19/18	D.N.		





NOTES:

MATERIALS:

- 1. INSULATORS = VIRGIN WHITE TEFLON PER ASTM D1710, GRADE 1, TYPE I, CLASS "B".
 2. ITERFACE CONTACT & SPRING = BERYLLIUM COPPER PER ASTM B196, ALLOY C17300, TEMPER TD04.
 3. ALL OTHER METAL PARTS = BRASS PER ASTM B16, ALLOY C36000, TEMPER H02.

FINISHES:

- 1. CONTACTS = GOLD PLATE PER ASTM B488-11, TYPE II, 50µin MIN, GRADE C, OVER 100 TO 200µin STRESS FREE SULFAMATE NICKEL PER AMS-QQ-N-290.

 2. ALL OTHE METAL PARTS = NICKEL PLATE PER AMS-QQ-N-290, CLASS 1, GRADE G, EXCEPT 100 TO 200µin THICK OVER 50 TO 100µin THICK COPPER PER AMS 2418.

UNLESS OTHERWISE SPECIFIE DIMENSIONS ARE IN INCHES TOLERANCES ON	DWN: DATE D.N. 04/19/18 CHKD: DATE		Property of Radiall This document cannot be reproduced or communicated to a third party without prior written permission of RADIALL.
DECIMAL ANGLE	C.E. 04/19/18 APVD: DATE J.M. 04/19/18	SLB RIGHT ANGLE FEMALE PLUG P.C.B MOUNT	
REFERENCE: ORIGINATED: D.N.	MATERIALS & FINISHES SEE NOTES	SIZE FSCM NO. 19505	DWG NO. 3042-7511-006 A
DATE: 04/19/18	SEE NOTES	scale 5:1	THIRD ANGLE SHEET 1 OF 1