



Electrical Specifications

Center Frequency: 2007.5 MHz
Bandwidth: 485 MHz
Passband: 1765-2250 MHz
Insertion Loss: 0.5 dB Max
Return Loss: 15 dB Min
Rejection: >30 dB @ 2312 MHz
Impedance: 50 Ohms In/Out
Power Handling: 20 W

Mechanical

Connector Type: SMA (F)
Dimensions: 6.78 x 1.58 x 1.38 Inches

Environmental

Operating Temperature: -30 to +75° C
Storage Temperature: -40 to +85° C
Shock: 20 G. 11 msec
Vibration: 20 G. 5 to 200 Hz

Outline Drawing:

