Precision Test Adapters

1.0 mm(F) to 1.85 mm(M)



Withwave's Precision Test Adapters are designed based on precision microwave interconnection technologies. This 1.0 mm(F) to 1.85 mm(M) adapter is manufactured to precise

microwave specifications and constructed with female gender on side 1 and male gender side 2.

The precision microwave connector interfaces ensure an excellent microwave performance up to 67 GHz



Features

- Frequency range : DC to 67 GHz
- VSWR : 1.2: 1(Max) @ 67 GHz
- Stainless steel (passivated)

Specification

Scope	Specification	AD00F01MS1
Electrical	Impedance(Ohm)	50
	Operation Freq.(GHz)	DC to 67 GHz
	VSWR (Max)	1.2 : 1
Material	Dielectric	Special dielectric
	Center Contact	Brass with gold plated
	Body	Passivated Stainless Steel

* RoHS Compliant


Precision Test Adapters

1.0 mm(F) to 1.85 mm(M)




Drawing

Part No.: AD00F01MS1



Test Result



• Frequency : 10 MHz to 67 GHz