
Data sheet | Item number: 855-4101/500-000 Split-core current transformer; Primary rated current: 500 A; Secondary rated current: 1 A; Rated power: 0.2 VA; Accuracy class: 0.5

www.wago.com/855-4101/500-000




Subject to changes. Please also observe the further product documentation!

WAGO Kontakttechnik GmbH & Co. KG Hansastr. 27 32423 Minden Phone: +49571 887-0 | Fax: +49571 887-169 Email: info.de@wago.com | Web: www.wago.com Do you have any questions about our products? We are always happy to take your call at +49 (571) 887-44222.







Item description

Short description:

WAGO's compact split-core current transformers are ideal for retrofitting existing systems. They are perfect for applications in which the current path must not be disrupted. The transformer's accuracy permits extremely precise current measurements. The split-core current transformers are capable of supplying the specified rated power at the end of the secondary cable. All transformers are supplied with color-coded cables. Two UV-resistant cable ties are also included for secure and easy mounting. **Features:**

- Current ratios from 500 A (primary side) and 1 A (secondary side)
- No measuring cable interruption
- Ideal for use in very confined spaces

Subject to changes. Please also observe the further product documentation!

WAGO Kontakttechnik GmbH & Co. KG Hansastr. 27 32423 Minden Phone: +49571 887-0 | Fax: +49571 887-169 Email: info.de@wago.com | Web: www.wago.com

Do you have any questions about our products? We are always happy to take your call at +49 (571) 887-44222.



- Rapid mounting
- For use around insulated cables up to 28 mm diameter
- Compact and hinged
- Color-coded connecting cable 3 m

Data

Technical data

Accuracy class	0.5
Primary rated current	500 A
Rated continuous thermal current I _{cth}	100 %
Rated short-time thermal current I _{th}	60 x I _N / 1 s
Rated surge current I _{dyn}	2.5 x I _{th}
Rated frequency	50 60 Hz
Secondary rated current	1A
Rated power S _r	0.2 VA

Safety and protection

Highest voltage for equipment U _m	AC 720 V _{rms}
Protection type	IP20
Test voltage	AC 3 kV; 50 Hz; 1 min

Connection data

Feedthrough for measurement conductor	Ø 28 mm
Cable type	2 x 0.5 mm²; fine-stranded
Color code	brown = S1; blue = S2

Physical data

Thysiodi data	
Cable length	3 m
Mechanical data	
Mounting type	Split-core current transformer (suspended)
Material data	
Flammability class per UL94	V2
Subject to changes. Please also observe the further product	t documentation!
WAGO Kontakttechnik GmbH & Co. KG	Do you have any questions about our products?
Hansastr. 27	We are always happy to take your call at +49 (571) 887-44222.
32423 Minden	
Phone: +49571 887-0 Fax: +49571 887-169	
Email: info.de@wago.com Web: www.wago.com	

www.wago.com/855-4101/500-000



Housing material	PA 66
Weight	350 g

Environmental requirements

Surrounding air temperature (operation)	-10 55 °C
Surrounding air temperature (storage)	-20 70 °C
Relative humidity	5 85 % (without condensation)
Operating altitude (max.)	2000 m

Standards and specifications

Conformity marking	CE
Standards/Specifications	EN 61869-1
	EN 61869-2

Commercial data

PU (SPU)	1 Stück
Packaging type	box
Country of origin	NL
GTIN	4055143950749
Customs tariff number	85043180888

Downloads Documentation

Bid Text

Did Text			
docx - Datei		docx 15.6 kB	Download
X81 - Datei		xml	Download
		5.5 kB	Download
Instruction Leaflet			
Kabelumbau-Stromwandler	V 1.1.0 Jan 15, 2020	pdf 832.5 kB	Download
Engineering-Software			
Software for Interface-Products			
WAGO Interface Configuration Software G2 FULL	1.0.7.9	exe	Download
Subject to changes. Please also observe the further product d	locumentation!		
WAGO Kontakttechnik GmbH & Co. KG	Do you have any questions about ou	ur products?	
Hansastr. 27	We are always happy to take your ca	all at +49 (571) 887-4	14222.
32423 Minden			

Phone: +49571 887-0 | Fax: +49571 887-169 Email: info.de@wago.com | Web: www.wago.com

Data sheet | Item number: 855-4101/500-000

www.wago.com/855-4101/500-000



Download

114.0 MB

exe

30.0 MB

The full setup, in addition to the WAGO Interface Configuration Software G2, includes Apr 8, 2021 the installation for the Microsoft .NET Framework. WAGO Interface Configuration Software G2 SMALL 1.0.7.9 Apr 8, 2021 The full setup only includes the WAGO Interface Configuration Software G2.

Environmental Product Compliance

Compliance Search

Environmental Product Compliance 855-4101/500-000	URL	Download
Split-core current transformer; Primary rated current: 500 A; Secondary rated current: 1 A; Rated power: 0.2 VA; Accuracy class: 0.5		

Installation Notes

Installation



Simple termination!

Quick and easy mounting!

Subject to changes. Please also observe the further product documentation!

WAGO Kontakttechnik GmbH & Co. KG Hansastr. 27 32423 Minden Phone: +49571 887-0 | Fax: +49571 887-169 Email: info.de@wago.com | Web: www.wago.com Do you have any questions about our products? We are always happy to take your call at +49 (571) 887-44222.