
12		11	10		9	8	7	6		5	4	3	2	1	
LOOSE PIECE			TAPE MOUNTED			SPECIFICATIONS									
MATER H NUMB		ENGINEERING NUMBER	MATERIAL NUMBER	ENGINEERING NUMBER	STUD SIZE	"S" ±.005 [0.13]	"W" ±.010 [0.25]	"C" MIN.	"L" MAX.	"Н"					
191780	800	BB-119-06			6	.146 [3.71]									
191780	010	BB-119-08	191780011	BB-119-08T	8	.173 [4.39]	.350 [8.89]	.271 [6.88]	.677 [17.20]	1.155 [29.34]					
191780	012	BB-119-10	191780013	BB-119-10T	10	.198 [5.03]									
G											-				




F

E

D

- NOTES:	
1. MATERIAL:	
TERMINAL: COPPER (STOCK TKN .031±.001 [0.79])	
B PLATING: ELECTRO-TIN (.0003 MIN).	В
2. WIRE SIZE: 16 -14 AWG	C AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION
$\frac{ SYMBOLS }{ IMENSION UNITS } = 0 \frac{ IMCH/MM }{ IMCH/MM } \frac{ SVMBOLS }{ IMCH/MM } = 0 \frac{ IMCH/MM }{ IMCH/MM } \frac{ IMCH/MM }{ IMCH/MM } = 0 \frac$	molex
3. "UL" LISTING #E32244	
"CSA" LISTING #18689	HOOK TONGUE TERMINAL
4. ALL DIMENSIONS IN INCHES/[MM]. 2019/09/13 2019/09/13 2019/09/13 2019/09/13 2019/09/13	KRIMPTITE 100-SERIES
▼ = 0 2 PLACES ± 0.13 ± .01 APPR: JMACNEIL 2019/10/18	PRODUCT CUSTOMER DRAWING
$\square ANGULAR TOL \pm 0.5^{\circ} APPR:$	BCD10102 PSD 001 A
BRAFT WHERE APPLICABLE THIRD ANGLE PROJECTION DRAWING SERIES MATERIAL NUME MUST REMAIN OF THE ADDRESS OF TACKNERS AND ADDRESS OF TACKNERS AND ADDRESS OF TACKNERS AND ADDRESS OF TACKNERS	
DOCUMENT STATUS P1 RELEASE DATE 2019/10/18 22:51:25 VITHIN DIMENSIONS 0 10 9 8 7 6 5 4 3	ABLE GENERAL MARKET 1 OF 1



F

Ε

D

PARTS ON TAPE