
THIS DRAWING CONTAINS INFORMATION PROPRIETARY TO RF INDUSTRIES, ANY UNAUTHORIZED USE OF THIS DRAWING IS EXPRESSLY PROHIBITED WITHOUT WRITTEN PERMISSION FROM RF INDUSTRIES. ANY VIOLATION IS PUNISHABLE UNDER U.S. COPYRIGHT LAWS.

ALL DIMENSIONS ARE REFERENCE ONLY

PAR	RFN-1013-1-03			
REV	DESCRIPTION	DWN	DATE	APPROVED
_	ENGINEERING RELEASE	JDM	2/6/98	JDM



## SPECIFICATIONS:

IMPEDANCE: 50 Ohms

FREQUENCY RANGE: 0-11 GHz

WORKING VOLTAGE: 1k V rms @ sea level TEMPERATURE RANGE: -65°C TO 165°C INSULATION RESISTANCE: 5k M Ohms min.

1	BODY	1	BRASS	NICKEL	008974		ί
2	INSULATOR	1	PTFE		1		l
3	CONTACT	1	PHOS BRONZE	GOLD			2
4	PRESS BODY	2	BRASS	NICKEL			3
5							14
6							5
7							6
8							L
9							ı
10					DRAWN JDM	10/11/11	ı
1 1					CHECKED	10/11/11	ı
12					CHECKED		ı
13					ORJ DRAWN	10/11/11	ı
14					C. ZUNIGA	10/11/11	ŀ
#	DESCRIPTION	QTY	MATRL	FINISH	APPROVALS	DATE	

UNLESS OTHERWISE SPECIFIED:

- 1. REMOVE ALL BURRS
- 2. BREAK ALL CORNERS & EDGES .005 R. MAX. 3. CHAMFER 1ST & LAST THREADS 45°
- 4. SURFACE ROUGHNESS 63 FINISH MIL-STD-10 5. DIAMETERS ON COMMON CENTERS TO BE
- CONCENTRIC WITHIN .002 T.I.R.
- 6. ALL DIMENSIONS ARE AFTER PLATING.

DIMENSIONS ARE IN INCHES AND [MILLIMETERS] UNLESS OTHERWISE NOTED

TOLERANCES ARE:

**DECIMALS** .XXX±.003 [.08] .XX±.005 [.13]

DIAMETER .XXX±.001 [.03] .XX±.003 [.08]



7610 MIRAMAR RD SAN DIEGO,CA 92126 (858) 549-6340 (858) 549-6345 FAX

## N JACK TO JACK

**ADAPTER** 

DWG NO. CABLE GROUP REV SIZE RFN-1013-1-03 CAD FILE OUTLINE SCALE: NTS SHEET 1 OF 1