



DANET	CUT OUT



	inches			
	Maxi	mini		
A	.198	.192		
В	.183	.177		

REVISIONS					
REV.	DESCRIPTION	DATE	APPROVED		
Α	INITIAL RELEASE	03/05/18	D.N.		



NOTES:

MATERIALS:

- 1. LOCKWASHER = PHOSPHOR BRONZE PER ASTM B139, COPPER ALLOY C53400, TEMPER H04.
 2. INSULATORS = VIRGIN WHITE TEFLON PER ASTM D1710, GRADE 1, TYPE I, CLASS "B".
 3. CRIMP SLEEVE = SEAMLESS LOWLEAD BRASS TUBE, ALLOY 330, SOFT ANNEAL TEMPER, .025/.060 GRAIN SIZE OR SEAMLESS COPPER TUBE PER ASTM B75, TYPE C12000, TEMPER: LIGHT ANNEAL 050 EXCEPT YIELD STRENGTH.
 4. ALL OTHER METAL PARTS = BRASS PER ASTM B16, ALLOY C36000, TEMPER H02.

FINISHES:

- 1. CONTACT = GOLD PLATE PER ASTM B488-11, TYPE II, 50µin MIN, GRADE C, OVER 100 TO 200µin STRESS FREE SULFAMATE NICKEL PER AMS-QQ-N-290.
 2. ALL OTHER METAL PARTS = GOLD PLATE PER ASTM B488-11, TYPE II, 30µin MIN, GRADE C OVER 100 TO 200µin COPPER STRIKE PER AMS 2418.

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ON		DWN: D.N. CHKD:	DATE 03/05/18 DATE		,	Property of Ro This document cannot be a communicated to a third p written permission of RADIA	reproduc		
DECIMAL ANGLE		C.E. APVD:	03/05/18 DATE	SMC STRAIGHT MALE JACK CRIMP TYPE					
		J.M.	03/05/18	FOR RG-316 & SIMILAR CABLES			LES		
REFERENCE: ORIGINATED: D.N.		MATERIALS & FINIS		SIZE A	FSCM NO. 19505	DWG NO. 1003-15	571-	-003	REV A
DATE: 03/05/18				SCALE	5:1	THIRD ANGLE PROJECTION	-	SHEET 1 O	F 1