

Summary

Request a quote

Cata	log

Coax	1
Socket / Receptacle	Socket / Receptacle - Elbow
Locking system	Push-pull
Matching parts	FFS.01.250.DLAE31

Technical details

Electrical Configuration

1
1.25 - 1 Coax (50 Ohm)
EPL.01 - Elbow receptacle for printed circuit
Elbow
Brass (gold plated [ISO 27874]) shell, collet nut, brass latch sleeve and mid pieces
Push-pull
Circular, female
3.17 g


$\underline{https://www.lemo.com/int_en/epl-01-250\text{-}dln.html}$

Environment

Environmental protection	IP50		
Minimal temperature	-55°C / +230°C		
Cable fixation			
Cable termination protection	Standard back nut (no additional protection)		
Fixation type	Cable collet		

Drawings







Dimensions

	A	L	М	В	С	D	N	
mm.	6	12.5	8.5	6	6	10	3	
in.	0.24	0.49	0.33	0.24	0.24	0.39	0.12	