Product data sheet Characteristics

SSL1A12BDRPV

Harmony, Solid state relay pre assembled, 2 A, random switching, screw sockets, input 16...30 V DC, output 24...250 V AC





Main

TTT COLL	
Range of Product	Harmony Solid State Relays
Product or Component Type	Solid state relay up to 10 A
Device short name	SSL
Phase	1 phase
Output switching mode	Random voltage switching

Complementary

o complementary	
Mounting Support	Screw socket
Line Rated Current	2 A
[Uc] control circuit voltage	1630 V DC
CLAMPING FORCE	< 0.5 N.m 4.4 lb-in
Connections - terminals	Flexible cable with cable end, 0.22.5 mm² AWG 24AWG 14) Solid cable with cable end, 0.22.5 mm² AWG 24AWG 14)
Capacitance unbalance	1.5 pF input/output
Minimum switching voltage	16 V DC turn-on
Maximum switching voltage	5 V DC turn-off
Input impedance	3.43 kOhm
Solid state output type	Random voltage switching SCR output
Load current	0.072 A
Tansient Overvoltage	600 V AC
Surge current	120 A 16.6 ms 115 A 20 ms
Maximum voltage drop	<1.1 V on-state
Maximum I²t for fusing	285 A ² .S for 10 ms at 50 Hz 260 A ² .s for 8.3 ms at 60 Hz
Maximum leakage current	4 mA off-state
DV/dt	500 V/µs off-state at maximum voltage
Response time	5 ms (turn-on) 10 ms (turn-off)
Overvoltage category	III
Width	0.24 in (6.2 mm)
Height	3.80 in (96.5 mm)
Depth	3.13 in (79.5 mm)
Net Weight	0.06 lb(US) (0.0285 kg)

Environment

Flame retardance	V0 conforming to UL 94
Dielectric strength	2500 V for input/output
Pollution degree	2
Standards	IEC 60950-1 IEC 61000 IEC 62314 IEC 61984 EN 61984
Product Certifications	UL CSA CE UL 508 CSA22.2 No. 14-10 GOST
Marking	CURus CSA CE EAC
IP degree of protection	IP20
Ambient Air Temperature for Operation	-4158 °F (-2070 °C)
Ambient Air Temperature for Storage	-4185 °F (-2085 °C)

Ordering and shipping details

a rate of the part	
Category	21127-ZELIO ICE CUBE RELAYS
Discount Schedule	CP2
GTIN	3606489563004
Nbr. of units in pkg.	1
Package weight(Lbs)	0.95 oz (27.0 g)
Returnability	Yes

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	0.20 in (0.5 cm)
Package 1 width	3.15 in (8 cm)
Package 1 Length	3.74 in (9.5 cm)
Unit Type of Package 2	BB1
Number of Units in Package 2	30
Package 2 Weight	31.22 oz (885.0 g)
Package 2 Height	3.54 in (9 cm)
Package 2 width	3.94 in (10 cm)
Package 2 Length	7.87 in (20 cm)


Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACh Regulation	REACh Declaration
REACh free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EPEU RoHS Declaration
Mercury free	Yes
RoHS exemption information	₫Yes
China RoHS Regulation	☑ China RoHS Declaration
Environmental Disclosure	Product Environmental Profile

Circularity Profile	End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Contractual warranty	
Warranty	18 Months

SSL1A12BDRPV


Dimensions



Product data sheet Performance Curves

SSL1A12BDRPV

Derating Curves



A: Load Current (Amperes)
B: Ambient Temperature (°C)