

### TECHNICAL DATA SHEET

# F727.754.710


LC DUPLEX PC MULTIMODE ADAPTOR ZIRCONIA ALIGNMENT SLEEVE


Packaging 100


Series LC


Issue 05/02/2011 Page 1/2


Adaptor: color AQUA Duplex











Scale: 1/1

Contents:

- Low profile duplex adaptor
- Receptacle dust capSleeve

Original dimensions in mm [inch]



## TECHNICAL DATA SHEET

## F727.754.710

LC DUPLEX PC MULTIMODE ADAPTOR ZIRCONIA ALIGNMENT SLEEVE

Packaging 100

Series LC Issue 05/02/2011

Page 2/2

Adaptor: color AQUA Duplex

### **GENERAL**

□ **TYPE** IEC 61754-20 (LC)

RJ-45 latching system Receptacle color : AQUA

☐ **MOUNTING** Snap-in mounting

Max. panel thickness 1.7 mm

□ ALIGNMENT SLEEVE Zirconia

#### **CHARACTERISTICS** (Depending on fibre or cable construction)

□ MATERIAL Plastic molded: Material in accordance with TELCORDIA GR-326 CORE

Inflammability V0 (UL 94)

□ **MECHANICAL** Durability 200 cycles

Plug Retention 68 N

□ ENVIRONMENTAL Storage temperature range -40 °C to +85 °C

Operating temperature range  $-40 \,^{\circ}\text{C}$  to  $+70 \,^{\circ}\text{C}$ 

□ **PROOF TEST** Straight pull 68 N

Side pull 23 N

□ VIBRATION TEST 10 to 55 Hz, 1,5 mm (peak to peak), 2 Hr/axis

(Performance and specification : see document GEN - F727 001)