



Electrical Specifications

Center Frequency: 3437.5 MHz
Bandwidth: 50 MHz
Passband: 3412.5-3462.5 MHz
Insertion Loss: 1.0 dB Max
Return Loss: 15 dB Min
Attenuation: >40 dB @ 2500 MHz
>35 dB @ (Fc ± 25) – 121 MHz
>50 dB @ (Fc ± 25) – 484 MHz
>50 dB @ (Fc ± 25) + 100 MHz
>40 dB @ 4000-10500 MHz

Power Handling: 25W

Mechanical

Connector Type: SMA (F)
Dimensions: 98 x 67 x 25 mm

Environmental

Operating Temperature: -40 to +85° C
Storage Temperature: -50 to +95° C

Outline Drawing:

