




SECTION: A-A
SCALE:1:1



SECTION: B-B
SCALE:1:1



Specifications_{XKB}

规格:

Voltage rating:500V AC/DC

额定电压: 500V AC/DC

Current rating:3A AC/DC

额定电流: 3A AC/DC

Withstanding voltage:1000V AC/minute

耐受电压: 1000V AC/分钟

Temperature range:-40℃-+85℃

温度范围: -40℃-+85℃

Insulation resistance:≥1000MΩ

绝缘电阻: ≥1000MΩ

Contact resistance:≤10mΩ

接触电阻: ≤10mΩ _{XKB}

After environmental testing:≤20mΩ

环境测试后: ≤20兆欧

X8821TF X-X SN X-L
① ② ③ ④ ⑤ ⑥ ⑦

- ① Series No.
- ② Category: T-Terminal
- ③ Appearance type: Blank-Ordinary
- ④ Material: P-Phosphor bronze; B-Brass
- ⑤ Plating Style: SN-Bright Tin Plating
- ⑥ Plating Method:
Blank-Stamping before Plating
B-Plating before Stamping
- ⑦ Mold No./Mark/Special No.: L-With Lock

X8821TF-BSN-L	Brass	AWG#22-26	1.90mm(Max)	Stamping Before Plating:30u" N;70u"Sn	X 8821HM-L
X8821TF-BSNB-L				Plating Before stamping:10u" N;40u"Sn	
X8821TF-PSNB-L	Phosphor Bronze	Plating Bfore Stamping:10u" Ni40u Sn			
X8821TF-PSN-L		Stamping Before Plating:30u" N;70c" Sn			
PART NO	Material	Wire Range	Insulation O.D.	Finish	Used In XKB Housing

DSND	SCALE: N/A	MODEL TYPE: 2.5mm Crimp Style Connector	
DWN	VIEW:	PART NO.: X8821TF-PSN-L	
CHKD	UNIT: mm/in	DWG NO.:	
APPD	SIZE: A4		
	WEIGHT	SHEET	REVISIC
		1/1	A0



XKB INDUSTRIAL PRECISION CO.,LIMITED

					ANGLAR	±5°
ΔX					L ≤ 4	±0.2
ΔX					4 < L ≤ 16	±0.3
ΔX					16 < L ≤ 63	±0.4
MARK					L > 63	±0.5
	DESCRIPTION	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES	
	REVISIONS					
	www.helloxkb.com www.helloxkb.cn www.xk-dg.cn					