



P.C.B LAYOUT

Specifications:

规格:
 Voltage rating:250V AC/DC
 额定电压: 250V AC/DC
 Current rating:1A AC/DC
 额定电流: 1A AC/DC
 Withstanding voltage:1000V AC/minute
 耐受电压: 1000V AC/分钟
 Temperature range:-40℃-+105℃
 温度范围: -40℃-+105℃
 Insulation resistance:≥1000MΩ
 绝缘电阻: ≥1000MΩ
 Contact resistance:≤20mΩ
 接触电阻: ≤20mΩ
 Material:PA6T UL94V-0
 材质: PA6T UL94V-0
 Plating Category:1U"Gold
 镀层: 1U"Gold
 Wave soldering temperature:255±5℃, 10S
 波峰焊温度: 255±5℃, 10S

X4621 W V - 2xXX I - C40 D28

① ② ③ ④ ⑤ ⑥ ⑦

- 1.Series No
- 2.Category:W-Wafer
- 3.Welding Board Angle:V-Straight 180°
- 4.Row No.Pin No:2xXX-2x01~2x40P
- 5.Plastic Height:l=2.0mm
- 6.Pin Length:C=4.0mm
- 7.Pin Length:D=2.8mm

X4621WV-2xXXI-C40D28	PA6T	Brass	X4621F
PART NO	Material	Material(Pin)	Suitable XKB Female

广东星坤科技股份有限公司

文件工程草

ANGLAR	±5°
L ≤ 4	±0.2
4 < L ≤ 16	±0.3
16 < L ≤ 63	±0.4
L > 63	±0.5
UNSPECIFIED TOLERANCES	



DSND		SCALE: N/A	MODEL TYPE: 2.0mm BTB Connector
DWN		VIEW:	PART NO.: X4621WV-2xXXI-C40D28
CHKD		UNIT: mm/in	DWG NO.: X-X4621WV-2xXXI-C40D28
APPD		SIZE: A4	WEIGHT SHEET REVISION 1/1 A0
KXB INDUSTRIAL PRECISION CO., LIMITED			