


P.C.B LAYOUT



SCHEMATIC

注：接触片分两种
1. 镀铜接触片
2. 磷铜接触弹线

SPECIFICATION

1. Rating: DC 12V 0.3A
 2. Travel: 2 mm
 3. Function: 1P2T
 4. Contact Resistance: $\leq 70m\Omega$ MAX
 5. Operating Force: $130\pm 30gf$, $200\pm 80gf$
 6. Life test: 10,000 cycles
- KNOB X=2, 3, 4, 4.3mm
TERMINAL Y = 2.0, 2.9, 3.9mm

				TOLERANCE UNLESS SPECIFIED										
				UP TO 5mm: ± 0.1	ANGULAR	A1	2019.08.02	更新PCB板开孔图		GYW				
				ABOVE 5mm: ± 0.2	$\pm 1^\circ$	A0	2019.01.10	首次发行		GYW				
						NO	DATE	REVISIONS		BY	APPD			
4	MK22D10 CONTACT/SPRING	BERYLLIUM/PBS	1	Ag PLATED/NATURAL	TITLE:MINI SLIDE SWITCH		UNIT : MM	ROHS COMPLIANT	DWN					
3	MS12D16 CASE 单边平脚	PA9T/0.3mm BRASS STRIP	1	BLACK/Ag(Ni) PLATED	MODEL:MS-12D16G2-B T2.9		SCALE: 6:1	CHK'D						
2	MS22D16 COVER 牙柄2X2	0.2mm SUS	1	WASHING	HAOYU(HONGKONG)LIMITED 皓宇(香港)有限公司							APPD		
1	MS22D16 KNOB	PA46/PA9T	1	WHITE/BLACK								PRO.AGL:		
NO.	PART NAME	MATERIAL	QTY	FINISHING										