



Specifications:

- 1.1 Current rating: 1 A Max.
- 1.2 Dielectric withstanding voltage: 500 V(ac) for 1 minute.
- 1.3 Contact resistance: 30mΩ Max.
- 1.4 Insulation resistance: 1000MΩ Min at DC 500V
- 1.5 Total mating force: 3.5 Kgf Max.
- 1.6 Total unmating force: 1.0 Kgf Min.
- 1.7 Temperature range: -20℃~+60℃.

电话: 0769-82320511-867

8					TOLERANCE								
7					UNLESS SPECIFIED								
6	SHELL-C	BRASS/Fe	1	Ni-PLATED	UP TO 5mm: ±0.1	ANGULAR	A1	2021.12.22	端子材质BRASS更新为PBS		WM		
5	SHELL-B	BRASS	1	Ni-PLATED	ABOVE 5mm: ±0.2	±1°	NO	DATE	REVISIONS		BY	APPD	
4	SHELL-A	BRASS/Fe	1	Ni-PLATED	TITLE: USB JACK			UNIT : MM	ROHS	DWN			
3	TERMINAL-B	PBS	4	Au/Sn-PLATED	MODEL: USB-302C-B-FE			SCALE: 1:1	COMPLIANT	CHK'D			
2	TERMINAL-A	PBS	4	Au/Sn-PLATED	<b>HAOYU(HONGKONG)LIMITED</b> 皓宇(香港)有限公司							APPD	
1	HOUSING	PBT(UL94V-0)	1	WHITE/BLACK									
NO.	PART NAME	MATERIAL	QTY	FINISHING								PRO.AGL:	REV :A1