





注：本板为禁止运输、复制、翻印文件，以及用其内容进行交流



REV	ECN NO.	CONTENT	CHK	DATE

NOTES1:
UL Standard
1.Rating voltage/current: 300V/8A
2.withstanding voltage: AC2000V/1Min
3.Torque value: M2.0, 1.77Lb.in
4.Wire range: 28~16AWG

IEC Standard

1. Pollution Degree	2
Overvoltage Category	III
Rate Impulse Voltage(KV)	2.5KV
Rate Voltage(V)	250V
Rate Current(A)	7A

2. Torque value: M2, 0.2Nm
3.wire range: 0.5~1.5mm²

NOTES2:
1.Housing: PA66 (UL94V-0)
2.Cover: PA66 (UL94V-0)
3.Cage: Brass (Ni Plated)
4.Clamp: Copper alloy (Ni Plated)
5.Screw: Steel (M2.0,Zn Plated)

NOTES3:
1.Pitch: 3.5mm Poles: 02-24P
2.Stripping length: 6-7mm
3.Operating temperature: -40℃~+105℃
4.RoHS Compliance

How to order
MX15EDGK - 35 - XXP - XXXX - XX - X - X

产品型号 间距 颜色 极数

灰色:GY 橙色:OE 01:常规颜色
蓝色:BU 红色:RD 定制颜色
黑色:BK 透明色:TT
绿色:GN 黄色:YW
透明色:TT 白色:WE

A-Z其他定制
0-Y一字螺丝
1-S十字螺丝
2-PS平头十字螺丝
Cu:铜方块
Fe:铁方块

Pitch Range In mm	Nominal Dimension Range In mm						Over 150	0.1/10
	Over 6	Over 10	Over 24	Over 30	Over 60	Over 100		
TO 6	TO 10	TO 24	TO 30	TO 60	TO 100	TO 150	∠	
±0.15	±0.20	±0.30	±0.30	±0.50	±0.70	±1.00	±1.30	

ITEM	NAME OF PART	NO. OF PART	Q'TY	MATERIAL	NOTE
DWG	CHK	DATE	UNITS	MM	1/1
APP	DATE	SCALE	SCALE	A4	1/1
CIXI MAIXU ELECTRONICS CO.,LTD				NAME	MX15EDGK-3.5-XXP
MAIXU 慈溪市迈旭电子有限公司				DWGNO.	