




RECOMMENDED P.C.B. LAYOUT

安装尺寸图



规格 Specifications

额定负荷 Rating	DC 12V/50mA
接触电阻 Contact Resistance	100mΩ max.
绝缘电阻 Insulation resistance	DC100V 60S 100MΩ min.
抗电强度 Dielectric strength	AC250V(50~60HZ) 60S min.
操作力 Operation force	250±50gf
寿命试验 Operating life	100,000cycles



CIRCUIT DIAGRAM

回路图

X. ± 0.3	X' ± 3'
.X ± 0.2	.X' ± 2'
.XX ± 0.1	.XX' ± 1'
.XXX ± 0.05	.XXX' ± 0.5'

5	COVER	1	LCP	BLACK
4	ACTUATOR	1	SILICONE	/
3	CONTACT	1	STAINLESS STEEL	Ag-PLATED
2	TERMINAL	2	BRASS	Ag-PLATED
1	HOUSING	1	LCP	BLACK
ITEM	PART NAME	QUANTITY	MATERIAL	FINISH



D-SWITCH
东莞市德松电子有限公司
D-SWITCH ELECTRONICS CO.,LTD

版本 VER.	变更说明 CHANGE DESCRIPTION	日期 DATE	ECN NO.	版本 VERSION	比例尺 SCALE	日期 DATE	品名 TITLE	图号 DRAWING NO
				核准 APPROVED BY	核对 CHECKED BY	绘图 DRAWN BY	DS-1TS009B-2500-4300	XXXXXXX
				A0	1:1	赵华玲		