



SPECIFICATION

1. Ratings: DC 12V 50mA Max
2. Contact resistance: 100mΩ MAX
3. Insulation resistance: 100MΩ Min
4. Dielectric strength: 250VAC/min
5. Operating force: 250gf± 50gf
6. Operating life: 100, 000 cycles

REFERENCE DRAWING

| UNSPECIFIED TOLERANCE | 6 | COVER (盖板) | 1 | SUS | |
|-----------------------|---------|-------------------|----------|---------------|-------------|
| 未指定的公差 | 5 | STEM (按钮) | 1 | H65 | YELLOW |
| ANGULAR (角度) | 4 | TAPE (防尘胶) | 1 | PI | — |
| 16 < L ≤ 63 | 3 | CONTACT FORM (弹片) | 1 | SUS301 | Ag plating |
| 4 < L ≤ 16 | 2 | HOUSING (基座) | 1 | PA6T | BLACK |
| L ≤ 4 | 1 | TERMINAL (端子) | 1 | H65 | Ag plating |
| | NO (序号) | PART NAME (部件名) | QTY (数量) | MATERIAL (材料) | REMARK (备注) |



D-SWITCH
东莞市德松电子有限公司
D-SWITCH ELECTRONICS CO.,LTD

| 版本 VER | 变更说明 CHANGE DESCRIPTION | 日期 DATE | ECN NO. | 版本 VERSION | 核准 APPROVED BY | 比例尺 SCALE | 核对 CHECKED BY | 日期 DATE | 绘图 DRAWN BY | 品名 TITLE | 图号 DRAWING NO |
|--------|-------------------------|---------|---------|------------|----------------|-----------|---------------|------------|-------------|------------------|---------------|
| | | | | A0 | | 1:1 | | 2022.12.08 | 孙成 | DS-TVCM15-010C-R | XXXXXXX |