



REFERENCE DRAWING

SPECIFICATION

1. Rating: DC 12V 50mA Max
2. Contact resistance: 100mΩ MAX
3. Insulation resistance: 100MΩ Min
4. Dielectric strength: 250VAC/min
5. Operating force: 180gf± 50gf
6. Operating life: 500,000 cycles

UNSPECIFIED TOLERANCE 未指定的公差		6	COVER (盖板)	1	SUS304	
		5	STEM (按钮)	1	H65	YELLOW
		4	TAPE (防尘胶)	1	PI	—
ANGULAR (角度)	± 0.5°	3	CONTACT FORM (弹片)	1	SUS301	Silver coated
16 < L ≤ 63	± 0.4	2	HOUSING (底座)	1	PA6T	BLACK
4 < L ≤ 16	± 0.3	1	TERMINAL (端子)	1	H65	Ag plating
L ≤ 4	± 0.2	NO (序号)	PART NAME (部件名)	QTY (数量)	MATERIAL (材料)	REMARK (备注)



版本 VER.	变更说明 CHANGE DESCRIPTION	日期 DATE	ECN NO.	版本 VERSION	A0	比例尺 SCALE	1:1	日期 DATE	2022.12.08	品名 TITLE	图号 DRAWING NO
				核准 APPROVED BY		核对 CHECKED BY		绘图 DRAWN BY	孙成	DS-TVCM17-015BY-R	XXXXXXX