



CIRCUIT DIAGRAM

P . C . B LAYOUT



.X: ±0.25	X°: ±8°
.XX: ±0.15	.X°: ±5°
.XXX: ±0.05	.XX°: ±2°

SPECIFICATIONS	
Operating temperature ranges	-30° to +85°
Rating	DC 12V 50mA Max.
Contact Resistance	100mΩ Max
Dielectric strength	250V AC for 1min.
insulation resistance	100mΩ Min. 100V DC
Operating force	100gf ± 40gf
Travel	0.2 ± 0.05mm
Operating Life (cycles)	100 000 CYCLES (1Ω Max)

NO.	NAME	MATERIAL	QTY	REMARK
1	TERMINAL	C2680	1	Ag plating(0.2 μm min)
2	CASE	PA9T	1	Black
3	CONTACT	SUS301	1	Ag plating(0.2 μm min)
4	COVER	SPCC	1	Cu/Sn Plating (Cu 2 μm min / Sn 1 μm min)
5	STEM	SILICA GEL	1	Bluc



版本 VERSION		A1		比例尺 SCALE		1:1		日期 DATE		2022.08.22		品名 TITLE		图号 DRAWING NO	
A 1	更新图纸							绘图		孙成		DS6060-050GJ		1190017	
版本 VER	变更说明 CHANGE DESCRIPTION	日期 DATE	ECN NO.	核准 APPROVED BY	核对 CHECKED BY	绘图 DRAWN BY									