



一. 电气性能:

- 1-1. 额定电流: 3A AC DC.
- 1-2. 接触电阻: $\leq 20m\Omega$
- 1-3. 绝缘电阻: $\geq 1000M\Omega$
- 1-4. 耐压: 550V AC/Minute

二. 物理特性:

- 2-1. 操作温度: $-55^{\circ}C \sim 105^{\circ}C$
- 2-2. 焊接温度: $+260^{\circ}C$, 10s max

三. 材质:

- 3-1. 塑胶: PA9T(Black) UL94V-0
- 3-2. 插针: Brass / gilt 3U"

PIN	A	B
1	2.54	0.00
2	5.08	2.54
3	7.62	5.08
4	10.16	7.62
5	12.70	10.16
6	15.24	12.70
7	17.78	15.24
8	20.32	17.78
9	22.86	20.32
10	25.40	22.86
11	27.94	25.40
12	30.48	27.94
13	33.02	30.48
14	35.56	33.02
15	38.10	35.56
16	40.64	38.10
17	43.18	40.64
18	45.72	43.18
19	48.26	45.72
20	50.80	48.26
21	53.34	50.80
22	55.88	53.34
23	58.42	55.88
24	60.96	58.42
25	63.50	60.96
26	66.04	63.50
27	68.58	66.04
28	71.12	68.58
29	73.66	71.12
30	76.20	73.66
31	78.74	76.20
32	81.28	78.74
33	83.82	81.28
34	86.36	83.82
35	88.90	86.36
36	91.44	88.90
37	93.98	91.44
38	96.52	93.98
39	99.06	96.52
40	101.60	99.06

图名:	2.54-2xNAT	未标注公差		绘制:	韩金锋	单位:	MM	
		XX.	± 0.40					XX.°
		X.	± 0.30	.XX°	$\pm 1^{\circ}$	签发:	比例:	1:1
		.X	± 0.20					
图号:	XXXXXXXXXXXXXXXXXXXX	.X	± 0.20	审核:		视图:		
		.XX	± 0.15					