

CS-1149-04KLVOW(0120)












CS-1149-04KRVOW(0120)

SPECIFICATIONS

- Voltage rating: 250V AC,DC
- Current rating: 7A,AC,DC
- Withstanding voltage: 1500V AC/minute
- Insulation resistance:1000MΩmin
- Temperature range:-40°C to+105°C
- Contact resistance:20mΩ max

HOUSING

- Part No:CS-1149-04KLVOW(0120)
/CS-1149-04KRVOW(0120)
- Poles:04+04
- Material:Nylon 66, UL94V-0,White
- Q'TY: 1000 pcs/bag



RoHS 2.0

本圖紙知識產權及版權由永丰盈有限公司所有,未經書面許可不准擅自傳閱、复制和修改.本公司保留法律追究的权利.

类别	HOUSING	品名	CS-1149-04KLVOW(0120)+CS-1149-04KRVOW(0120)			材料	单位	mm	SHEET 1 OF 1		
版本	A/0	设计	李文畅	X.X	±0.40	颜色	比例	1:1	▲	修改内容	修改日期
制定部门	工程课	绘制	李文畅	X.XX	±0.30	画法	数量		▲		
工程图号	CS-1149	审核	姚培柱	X.XXX	±0.20	CST	深圳市永丰盈电子有限公司 ShenZhenYongFengYing ELECTRONIC CO.,LTD.			▲	
制定日期	2018-04-02	核准	周中湖	X.XXXX	±0.10					▲	