

1 2 3 4 5 6 7 8

A

B

C

D

E

■ SPECIFICATIONS

- Poles:20
- Voltage rating: 250V AC,DC
- Current rating: 7A, AC, DC
- Withstanding voltage: 1500V AC/minute
- Insulation resistance:1000MΩ min
- Temperature range:-40°C to +105°C
- Contact resistance:20mΩ max

■ HOUSING








- Poles:20+4
- Material:Nylon 66, UL94V-0
- Q' TY: 500 , 1000 pcs/bag
- Part No. :CS-1149-20 E V0 W (0114)

企业Logo
产品料号
产品PIN位
滑轨型号代码
材质
V0:PA66-V0

色粉号: 0114
颜色
B:黑色
N:本色
W:白色
L:蓝色

企业Logo
产品料号
产品PIN位
滑轨型号代码
材质
V0:PA66-V0

色粉号: 0114
颜色
B:黑色
N:本色
W:白色
L:蓝色



本圖紙知識產權及版權由巧盛企業有限公司所有,未經書面許可不准擅自傳閱、复制和修改。本公司保留法律追究的权力。

SORT	HOUSING	PART NO.	CS-1149-20EV0W (0114) +04EV0W (0114)			MATERIAL	UNIT	mm	SHEET 1 OF 3		
VERSION	B/1	DESIGNER	WENCHANG LI	X. X	±0.40	COLOUR	SCALE	1:1	▲	REVISE	REVISE DATE
FRAME	ENGINEER DEPARTMENT	DRAW BY	WENCHANG LI	X. XX	±0.30	PROJECTION	QUANTITY	▲	1	10.8±0.1改 10.8±0.2	2023-04-07
DRAWING NO.	CST-H01149E	CHECK BY	PEIZHU YAO	X. XXX	±0.10	CST 深圳市永丰盈电子有限公司 ShenZhenYongFengYing ELEELECTRONICS CO.,LTD.	▲	2			
DATE	2023-04-07	APPROVE	CUI MIN	X. XXXX	±0.05		▲	3			

1 2 3 4 5 6 7 8