



Recommended P. C. B  
Layout(±0.05)

Technical Date  
 Pin(outer sleeve):Brass,machined CuZn38pb2  
 Clip (Contact 4 Finger):Beryllium copper,heat treated  
 Insulator:PBT UL94V-0 colour:black  
 Gold Plated:2um"/80u"Ni,GF  
 Current rating:3Amps  
 Mechanical Life:min 500 cycles  
 Contact resistance: 10mΩ max  
 Dielectric strength:1000V  
 Operating temperature:-40 °C to +105°C  
 Soldering temperature:+255°C

X5621 F V -2xXX- C762 D1150 -1150  
 ① ② ③ ④ ⑤ ⑥ ⑦

- 1.Series No
- 2.Category:F-Female
- 3.Welding Board Angle:V-Straight 180°
- 4.Row No-Pin No:2xXX-2x01Pin-2xXXPin
- 5.line spacing:C=7.62mm
- 6.Pin Length:D=11.50mm
- 7.1150:Type1150

X5621FV-2xXX-C762D1150-1150	PBT	Brass	X5621W
PART NO	Material	Material(Pin)	Suitable XKB Wafer

广东星坤科技股份有限公司

生  
查  
MARK

日期

DESCRIPTION

REVISIONS

www.helloxkb.com www.helloxkb.cn www.xk-dg.cn

ANGULAR	±5°
L ≤ 4	±0.2
4 < L ≤ 16	±0.3
16 < L ≤ 63	±0.4
L > 63	±0.5
UNSPECIFIED TOLERANCES	



DSND

SCALE: N/A

MODEL TYPE:  
2.54mm BTB Style Connector

DWN

VIEW:

PART NO.:  
X5621FV-2xXX-C762D1150-1150

CHKD

UNIT: mm/in

DWG NO.:  
X-X5621FV-2xXX-C762D1150-1150

APPD

SIZE: A4

WEIGHT	SHEET	REVISION
	1/1	A0

XKB INDUSTRIAL PRECISION CO.,LIMITED

文件工程章