





RoHS

REV.	ECN NO.	DESCRIPTION	DESIGN	APPROVAL	DATE
A1	NEW	更换图框			2023.09.05

No. of Pin/Row	Dimension	
	A	B
2X02	1.27	2.54
2X03	2.54	3.81
2X04	3.81	5.08
2X05	5.08	6.35
2X06	6.35	7.62
2X07	7.62	8.89
2X08	8.89	10.16
2X09	10.16	11.43
2X10	11.43	12.70
2X11	12.70	13.97
2X12	13.97	15.24
2X13	15.24	16.51
2X14	16.51	17.78
2X15	17.78	19.05
2X16	19.05	20.32
2X17	20.32	21.59
2X18	21.59	22.86
2X19	22.86	24.13
2X20	24.13	25.40
2X21	25.40	26.67
2X22	26.67	27.94
2X23	27.94	29.21
2X24	29.21	30.48
2X25	30.48	31.75
2X26	31.75	33.02
2X27	33.02	34.29
2X28	34.29	35.56
2X29	35.56	36.83
2X30	36.83	38.10
2X31	38.10	39.37
2X32	39.37	40.64
2X33	40.64	41.91
2X34	41.91	43.18
2X35	43.18	44.45
2X36	44.45	45.72
2X37	45.72	46.99
2X38	46.99	48.26
2X39	48.26	49.53
2X40	49.53	50.80
2X41	50.80	52.07
2X42	52.07	53.34
2X43	53.34	54.61
2X44	54.61	55.88
2X45	55.88	57.15
2X46	57.15	58.42
2X47	58.42	59.69
2X48	59.69	60.96
2X49	60.96	62.23
2X50	62.23	63.50



P.C.B Hole Layout

技术参数 (SPECIFICATIONS)

- 额定电流(Current rating) : 1A
- 耐压值(Withstand voltage) : 500V AC
- 绝缘电阻(Insulation resistance) : 500M
- 接触电阻(Contact resistance) : 20m
- 工作温度(Working temperature) : -40 ~ +105

材料 (MATERIAL)

- 绝缘体(Insulator Material) : PA6T UL 94V-0 Black
- 接触材料(Contact Material): Brass Gold-Flash Plated
- 匹配型号(Matching model) : PM127 series

项目	H	PC	PA	W	SQ		
常规尺寸	1.0	2.2	4.0	3.4	0.4		
客户需要							

产品名称说明 :

PZ127V-12-xx-0720
1 2 3

1. 序列号
2. Pin位数: 02-100Pin
2x02=04
3. 针长: 7.2=0720

X.±0.50	X.°±
.X±0.25	.X°±
.XX±0.15	.XX°±
.XXX±0.10	.XXX°±
UNITS:	mm

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF XFCN AND SHALL NOT BE REPRODUCED, COPIED OR CUED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF XFCN

PART NO.:	PZ127V-12-xx-0720
TITLE:	1.27mm 排针 双排 直型 4.0(1.0)2.2
APPD:	
CHKD:	Zhi Qiang.Chen 2023.09.13
DRAW:	Tong.Deng 2023.09.11

XFCN 兴飞连接器		
0769-82001899		
www.xfconn.com		
DWG NO: /		

	SCALE	SHEET	REV.
	NONE	1/1	A1