






HF

Halogen Free

REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
X1			INITIAL RELEASE	2022.02.17	JACKY
X4		1/4	增加 DATECODE	2022.11.03	tanghaibo
X5		1/5	新增料号编码	2022.12.19	tanghaibo
X6		1/6	修改编码电镀选项	2023.02.18	tanghaibo




RECOMMEND PC BOARD HOLE PATTERN:
CONNECTOR MOUNT SIDE
(NOT ACCUMULATE TOLERANCE)
PC BOARD THICKNESS: 1.0~1.6±0.10



40POS: 5617BG-003H***V000

- MATERIAL: HOUSING: GLASS FILED THERMO PLASTIC POLYESTER(94V-0)
COLOR: BLACK OR WHITE
CONTACT: COPPER ALLOY
RETENTION PEG: PRE-TIN COPPER ALLOY
- FINISH(ALL OVER): NICKEL PLATING 1.27um MIN
- FINISH(CONTACT AREA): GOLD PLATING TIN SPECIFICATIONS
REFER TO THE FOLLOWING MATERIAL NUMBER CODE SPECIFICATIONS
- FINISH(CONTACT TAIL): TIN PLATING 2um MIN AFTER
- THE SHAPE, SIZE AND POSITION OF THE CHARACTER SHOW THE OUTLINE.
THEY DON'T SHOW DETAILS
- DATECODE: YYWWD
YY: YEAR(22: 2022)
WW: WEEK(25: THE 25TH WEEK)
D: DAY(1~7: SUNDAY~SATURDAY)
- PART NO.: 56**BG-***H * * * * V000



40	X	19	38.0	41.0	42.6	5617BG-003H***V000	5617BG-001H***00000
34	X	16	32.0	35.0	36.6	5611BG-002H***V000	5611BG-003H***00000
30	X	14	28.0	31.0	32.6	560WBG-003H***V000	560WBG-001H***00000
26	X	12	24.0	27.0	28.6	560SBG-005H***V000	560SBG-002H***00000
22	X	10	20.0	23.0	24.6	560NBG-001H***V000	560NBG-002H***00000
20	X	9	18.0	21.0	22.6	560LBG-005H***V000	560LBG-002H***00000
POS	KEY	n	A	B	C	MALE PART NO.	FEMALE PART NO.

DIM	TOL	DIM	TOL
x.	±0.50	x.	±5'
.x	±0.35	.x	±3'
.xx	±0.30		










DEREN
SHENZHEN DEREN ELECTRONIC CO., LTD

DRAW NO.	DESIGN: Tanghaibo	DATE: 2023.02.18	TITLE: WTB Male XXP 15H Pitch2.0 180DIP ASSY
	CHECK:		P/N: 56**BG-***H***V000
REV. X6	APPROVAL:		SHEET: 1/3
			SCALE: 1:1 UNIT: mm

HF

Halogen Free

REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
X1			INITIAL RELEASE	2022.03.01	JACKY
X4			增加 DATECODE	2022.11.03	Tanghaibo
X5			新增料号编码	2022.12.19	Tanghaibo
X6			修改编码电镀选项	2023.02.18	Tanghaibo



34POS: 5611BG-002H***V000

30POS: 560WBG-003H***V000

26POS: 560SBG-005H***V000

DIM	TOL	DIM	TOL
x.	±0.50	x.	±5'
.x	±0.35	.x	±3'
.xx	±0.30		

**DEREN**

SHENZHEN DEREN ELECTRONIC CO., LTD

INSPECTION	DRAWING	DATE	TITLE:
DESIGN:	Tanghaibo	2023.02.18	WTB Male XXP 15H Pitch2.0 180°DIP ASSY
CHECK:			P/N: 56**BG-***H***V000
APPROVAL:			SHEET: 2/3
REV. X6			SCALE: 1:1 UNIT: mm

1

2

3

4

5

6

7

8

A

B

C

D

E

A

B

C







D

E

HF

Halogen Free


REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
X1			INITIAL RELEASE	2022.03.01	JACKY
X4		1/4	增加 DATECODE	2022.11.03	Tanghaibo
X5		1/4	新增料号编码	2022.12.19	Tanghaibo
X6		1/4	修改编码电镀选项	2023.02.18	Tanghaibo



20POS: 560LBG-005H****V000

22POS: 560NBG-001H****V000

DIM	TOL	DIM	TOL
x.	±0.50	x.	±5'
.x	±0.35	.x	±3'
.xx	±0.30		



DEREN
SHENZHEN DEREN ELECTRONIC CO., LTD

INSPECTION	DRAWING	DATE	TITLE: WTB Male 22~40P 15H Pitch2.0 180DIP ASSY
DESIGN:	Tanghaibo	2023.02.18	P/N: 56**BG-****H****V000
CHECK:			SHEET: 3/3
APPROVAL:			SCALE: 1:1 UNIT: mm

DRAW NO.

REV. X6

