



PCB LAYOUT

SPECIFICATIONS

- 1、Current Rating: 7A AC, DC
- 2、Voltage Rating: 250V AC, DC
- 3、Temperatuer Range: -25°C~+85°C
- 4、Contact Resistance: 20mΩ Max
- 5、Insulation Resistance: 1000MΩ Min
- 6、Withstanding Voltang: 1500V AC/minute
- 7、Material: Wafer Nylon66, UL94V-0  
PIN Brass Tin-plated

编号	尺寸 (MM)	
	A	B
YTC-A3961-02A	3.96	7.92
YTC-A3961-03A	7.92	11.88
YTC-A3961-04A	11.88	15.84
YTC-A3961-05A	15.84	19.80
YTC-A3961-06A	19.80	23.76
YTC-A3961-07A	23.76	27.72
YTC-A3961-08A	27.72	31.68
YTC-A3961-09A	31.68	35.64
YTC-A3961-10A	35.64	39.60
YTC-A3961-11A	39.60	43.56
YTC-A3961-12A	43.56	47.52

版本	变更内容	工程确认	日期

深圳市怡远科技有限公司 SHENZHEN YIYUAN TECHNOLOGY CO., LTD		页码 (SHEET)	1/1	单位 (UNIT): MM
		版本 (REV)	A1	比例 (SCALE)
品名 (ITEM NO)	VH直针 VAFER DIP TYPE	日期 (DATE)	2021. 10. 12	
料号 (PART NO)	YTC-A3961-NA	设计 (DESIGN)	LUO	
图号 (DWG NO)		审核 (CHECKED)	ROGER LI	GENERAL TOLERANCE X.±0.25 X.±2' .XX±0.20 .XX±1' .XX±0.15 .XX±0.5' .XXX±0.10 .XXX±0.5'
		核准 (APPROVED)	ROC ZHAO	

These drawings and specifications are Shenzhen Yiyuan Technology Co Ltd. The property should not be copied. Without Shenzhen Yiyuan Technology Co. Ltd. Prior written consent to copy or use in any way. Email at info@yiyuanswitches.com