
	I	Q		П			O		₿ ♪		
4		V Thread	ØS								4
ω							LAY	OUT SHOWN AS EXAMF	PLE		3
Keying Shown as example											
	CHARACTERISTICS			Connector dimension Dim Nomir							
N	-Standard : Based on MIL-DTL-38999 -Shell Material : Composite -Shell Plating : Nickel -Insulator : Thermopla -Contacts : Copper All -Seals & Grommet : Silicon Ela -Contact Plating : Gold over	e astic loy	n	SOURIAU shall not be liable for any non-conformity or damage due to a use of the Products which does not comply with the Specifications issued by either of the Parties or by a third party (professional recommendation, technical notice.) Country Jurisdiction & Control List FR Not Listed					2		
	-Durability : 500 Matin -Delivered without Souriau contacts			PN: 8D525M29SAL							
	-Temperature Range : -65°C to + -Salt Spray : 2000 hour					A 07-10-201	.6 First Release				-
	-Mass : 55.9 g ± 10)%				ISS DATE Designed By:	Latest modification	n - by	CUSTOMER DRAWING	MOD N°	
				TITLE	TLE Composite Plug 8D series			_			
→	BASIC SERIES: SHELL TYPE : Plug with RFI Shieldin		M 29 S A L	Delive	red W/O Contacts	SCALE NA		General linear Tolerances: ±	NPRDS / PROJECT 859		1
	CONTACT TYPE : Standard Crimp Contact SHELL SIZE : 25 CONTACT TYPE : SOCKET(500 Matings)						U WWW.SOURIAU.COM it must not be repro- communicated without		uced or		
	PLATING : M = Nickel				CT LAYOUT : 25-29	FORMAT A3		SOURIAU DE	RG N°	SHEET	-
	H	G	F	E			С	8D525M29S	SAL-C	1/2	
		<u>.</u>	. 1	-	\vee						



		σ		А				
						4		
						4		
						0		
						3		
all not be liab use of the Pro	-			e				
ons issued by	either of th	ne Parties or l	oy a third pa	irty				
essional recon	imendatio	n, technical n	otice.)					
CountryJurisdiction & Control ListFRNot Listed								
			NOT LISTED	4		2		
PN: 8D5	525M2	29SAL						
ation - by te:			CUSTOM	ER DRAWING	MOD N°	 		
C	omposi	te Plug 8	D series					
Genera	l linear		NPRDS	/ PROJECT				
Tolerances: ±			859					
			This do	ocument is the pro	perty of			
W.SOURIAU.COM SOURIAU it must not be reproduced or								
COLLEIALI DEC Nº SHEET								
JOUNIAU DINU N								
8052	2510129	JSAL-C		A	2/2	J		
		В		А				