


REVISIONS					
REV	ECO	DESCRIPTION	DATE	BY	APPR
A 1	-	FIRST RELEASE	Oct.22,2015	Drack	Tommy
A2	-	Updated Drawing	Jun.20,2017	White	Tommy




22.6 28.0

28.0 22.6







PANEL SEAL RING DETAIL

E TYPE, NORMAL KEY

NOTES: UNLESS OTHERWISE SPECIFIED

1. MATERIAL:

INSULATION INSERT: PA66,UL94 VO

SEAL: VITON

HOUSING BODY: ZINC DIE CAST, NICKEL PLATED

2. SPECIFICATIONS

2.1 CURRENT RATING: 9 AMPS

2.2 VOLTAGE RATING: 125 V AC/DC

2.3 OPERATING TEMPERATURE: -20C TO +130C

2.4 DIELECTRIC WITHSTANDING VOLTAGE: LESS THAN 2 MILLIAMPS CURRENT LEAKAGE @ 2500 VOLTS AC.

2.5 DEGREE OF PROTECTION: IP67 (MATED CONDITION)

2.6 DEGREE OF POLLUTION: 3 PER UL840


2.7 OVERVOLTAGE CATEGORY: III PER UL840


2.8 MATING CYCLE DURABILITY: >500 CYCLES

2.9 RoHS COMPLIANT

3. ALL DIMENSIONS ARE FOR REFERENCE USE ONLY.

22.6 22.6 MOUNTING HOLE





M23A,REC.,RA,17P,E TYPE, CHECKMATE

DWG NO:

MA5RAE1702

22