

	Φ		A			
	81/				4	
		/				
	1	1				
S EXAM	PLE				3	
anv nor	1-conformit	v or damage				
which c	any non-conformity or damage which does not comply with					
	r of the Parties or by a third party dation, technical notice.)					
Intry R	ry Jurisdiction & Control List Not Listed					
I					2	
SW04SNL						
		CUSTOMER	R DRAWING	MOD N°		
um Re	m Receptacle 8D series					
ar	NPRDS / PROJECT					
		8	59		1	
.COM						
		it must not be reproduced or communicated without permission				
U DRG N° V04SNL-C				SHEET 1/2		
043	B B		A	-, -	J	

r	<b></b>	۵	п	т		0	
		Contact Layout				Panel cutout	
4						JAM NUT RECEPTACLE (TYPE 7)	
	B  +203 (5-16)  +    C  +324 (823)  -    D  +424 (10.77)  -    E  +493 (12.52)  -    F  +531 (13.49)  -    G  +531 (13.49)  -    H  +493 (12.52)  -    J  +424 (10.77)  -    K  +324 (8.23)  -    L  +203 (5.16)  -	Y-axis (mm)  Contact position ID  X-axis (mm)  Y-axis (mm)    531 (13.49)  f  +412 (10.46)  +000 (0.00)    +495 (12.57)  g  +377 (9.58)  -132 (3.35)    +425 (10.80)  h  +311 (7.90)  -251 (6.38)    >326 (8.28)  k  +212 (5.38)  -344 (8.74)    >205 (5.21)  m  -086 (2.18)  -397 (10.08)    0.696 (1.75)  p  -212 (5.38)  -344 (8.74)    -205 (5.21)  q  -311 (7.90)  -251 (6.38)    -326 (9.28)  r  -337 (10.08)  -344 (8.74)    -326 (9.28)  r  -311 (7.90)  -251 (6.38)    -326 (9.28)  r  -377 (9.58)  -132 (3.35)    -425 (10.80)  s  -412 (10.46)  +000 (0.00)    -425 (10.80)  s  -412 (10.46)  +000 (0.00)				ØC	
ယ	N 069 (1.75)    P 203 (5.16)    R 324 (8.23)    S 424 (10.77)    T 493 (12.52)    U 531 (13.49)    V 531 (13.49)    W 493 (12.52)    Contact  Location	-531 (13.49)  v  -212 (5.38)  +344 (8.74)    -495 (12.57)  w  -086 (2.18)  +397 (10.08)    -425 (10.80)  x  +009 (1.75)  +263 (6.68)    -326 (8.28)  y  +172 (4.37)  +149 (3.78)    -205 (5.21)  z  +268 (6.55)  +000 (0.00)    -099 (1.75)  BB  +.069 (1.75)  -263 (6.68)    +205 (5.21)  CC 069 (1.75)  -263 (6.68)    -205 (5.21)  CC 069 (1.75)  -263 (6.68)    -205 (5.21)  CC 069 (1.75)  -263 (6.68)    Contacts  (insert arrangement 25-4)  u  Location				Dim  Nomina    B  43.43+0/-0    ØC  44.7+0.25	0.25
	Y324 (8.23) Z203 (5.16) a069 (1.75) b + .086 (2.18) c + .212 (5.38) d +.311 (7.90)	T-aus  position ID  A-aus  T-aus    (mm)  (mm)  (mm)  (mm)    +326 (8-28)  DD  -172 (4.37)  -149 (3.78)    +425 (10.80)  EE  -258 (6.55)  +.000 (0.00)    +425 (13.49)  GG 069 (1.75)  +263 (6.83)    +337 (10.08)  HH  +.000 (0.00)  +.132 (3.85)    +344 (8.74)  JJ  +.086 (2.18)  +.000 (0.00)    +251 (6.38)  KK  +.000 (0.00) 132 (3.35)    +.132 (3.35)  LL 086 (2.18)  +.000 (0.00)	1			SOURIAU shall not be lia	
	size no. conta 25 -4 8 48	16 J, z, AA, DD, EE, FF, LL, JJ MS20057-4				due to a use of the Pr the Specifications issued b (professional reco	by either of t
N							Country FR
						PN: 8D	072500
					ISS DATE Designed By:	Latest modification - by Date:	
					SCALE		minium ral linear
<u> </u>					NA	-{	erances: ±
					SOURIA	U WWW.SOUF	RIAU.CO
					FORMAT A3		JRIAU 725W0
L	Н	G	F	E	D	С	

Φ	A				
T			4		
L			3		
any non-conformit which does not co or of the Parties or b dation, technical no intry Jurisd R SWO4SNL	mply with by a third party		2		
	CUSTOMER DRAWING	MOD N°			
um Receptacle 8D series					
ar	NPRDS / PROJECT 859	portu of	1		
I.COM	This document is the prop SOURIAU it must not be reproduc communicated without pe	ed or rmission			
U DRG N° V04SNL-C	SHEET 2/2				
B	A				