

	Φ			A		
						4
S EXA	MPLE					3
whic er of tl idatio	non-conformit h does not co he Parties or b n, technical n	mply wit by a thiro otice.)	th d party			
Intry R	46BE	Not Li	Control sted	LIST		2
		CUST	OMER D	RAWING	MOD N°	
um	m Receptacle 8D series					
ar		NPI	RDS / PR <b>859</b>	OJECT		
	.COM This document is the property of SOURIAU it must not be reproduced or communicated without permission			ed or	1	
U DRG N° W46BE-C					SHEET	
vv4	B B			A	1/2	J

_	I	G	г	m	D	0	
		Contact Layout				Panel cutout	
4	$ \begin{array}{c} \overset{\overset{\overset{\overset{\overset{\overset{}}}}{\underset{\underset{\underset{}}{\overset{\overset{}}}}}} = \frac{2}{\sqrt{2}} \frac{1}{\sqrt{2}} \frac{1}{\sqrt{2}}$	$ \begin{array}{c} \overset{r_{0}}{\longrightarrow} & \overset{r_{0}}$				JAM NUT RECEPTACLE (TYPE 7)	A
_	(Inactive for new design for M	IIL-DTL-38999. For new design, use arrangement no. 25-47.)           Contacts           (Insert arrangement 25-46)           n           Location	-				/ v
c.s	Dosition ID         X-axis (mm)           A         +.065 (1.65)           B         +.275 (6.99)           C         +.420 (10.67)           D         +.490 (12.45)           E         +.531 (13.49)           F         +.531 (13.49)           G         +.490 (12.45)           H         +.420 (10.67)           J         12.75 (6.99)           K         +.065 (1.65)           L        065 (1.65)           M        275 (6.99)           N        420 (10.67)           P         -490 (12.45)           R        531 (13.49)           T        490 (12.45)           U        420 (10.67)           P        490 (12.45)           U        420 (10.67)           V        275 (6.99)           W        005 (1.65)           X         +.136 (3.45)           V        275 (6.99)           W        005 (1.65)           X         +.136 (3.45)           Y         +.224 (6.22)           Z         +.314 (7.98)	Y-axis (mm)         Contact position ID         X-axis (mm)         Y-axis (mm)           533 (13-54) <u>a</u> +404 (10 26)         +125 (3.18)           +466 (11.84) <u>b</u> +437 (11.10)         +000 (0.00)           +337 (0.56) <u>c</u> +404 (10 26)         +125 (3.18)           +227 (5.77) <u>d</u> +314 (7.98)         -221 (5.61)           +093 (2.36) <u>e</u> +245 (6.22)         -337 (8.56)           -093 (2.36) <u>f</u> +136 (3.45)         -424 (10.77)           -227 (5.77) <u>g</u> +000 (0.00)         -358 (10.33)           -337 (8.56) <u>h</u> -316 (7.98)         -221 (5.61)           -533 (13.54) <u>m</u> -314 (7.98)         -221 (5.61)           -533 (13.54) <u>m</u> -314 (7.98)         -221 (5.61)           -337 (8.56) <u>g</u> -404 (10.26)         -125 (3.18)           -466 (11.84) <u>p</u> -437 (11.10)         +000 (0.00)           -337 (8.56) <u>g</u> -245 (6.22)         +337 (8.56)           -993 (2.36) <u>i</u> -136 (3.45)         +424 (10.77)           +227 (5.77) <u>g</u> +007 (2.46)         +265 (6.73)				Dim Nomina B 43.43+0/-0 ØC 44.7+0.25,	.25
	25 -46 2	Size         Service         Contact         Standard contact           Instacts         rating         location         Pin         Socket           8         (see         Coax         z, w         M39029/60-367         M39029/50-366	5			SOURIAU shall not be lial	
	4	AA, 16         AA, y, X, y         M39029/58-364         M39029/56-352           20         All others         M39029/58-363         M39029/56-351				due to a use of the Pro the Specifications issued by (professional reco	y either of
N							Country FR
						PN: 80	)725W
					A 05-10-20 ISS DATE	16 First Release Latest modification - by	
					Designed By:	Date:	
					TITLE	Alur	minium
<b>→</b>					SCALE NA		al linear rances: ±
					SOURIA	U WWW.SOUF	RIAU.CO
					FORMAT A3		IRIAU 725W4
L	Н	G	F	E	D	C C	

σ						
Γ		4				
L						
		3				
any non-conformit which does not co or of the Parties or I dation, technical n intry Jurisc R 5W46BE	mply with by a third party	2				
um Recentac	CUSTOMER DRAWING	J°				
ir	Receptacle 8D series NPRDS / PROJECT 859					
.COM	This document is the property of SOURIAU it must not be reproduced or communicated without permission	1				
U DRG N° W46BE-C	SHEET 2/2					
В	A					