


PCB LAYOUT

SPECIFICATIONS

1. Current Rating: 2A AC, DC
2. Voltage Rating: 250V AC, DC
3. Temperature Range: -25°C ~ +85°C
4. Contact Resistance: 20mΩ Max
5. Insulation Resistance: 1000mΩ Min
6. Withstanding Voltage: 1000V AC/minute
7. Material: Wafer LCP, UL94-V0
PIN Brass Tin-plated
Solder pad Phosphoric bronze Tin-plated

Circuit	Part NO.	Dimensions mm	
		A	B
2	HC-HY-2ALT-X	2.00	8.00
3	HC-HY-3ALT-X	4.00	10.00
4	HC-HY-4ALT-X	6.00	12.00
5	HC-HY-5ALT-X	8.00	14.00
6	HC-HY-6ALT-X	10.00	16.00
7	HC-HY-7ALT-X	12.00	18.00
8	HC-HY-8ALT-X	14.00	20.00
9	HC-HY-9ALT-X	16.00	22.00
10	HC-HY-10ALT-X	18.00	24.00
11	HC-HY-11ALT-X	20.00	26.00
12	HC-HY-12ALT-X	22.00	28.00
13	HC-HY-13ALT-X	24.00	30.00
14	HC-HY-14ALT-X	26.00	32.00
15	HC-HY-15ALT-X	28.00	34.00
16	HC-HY-16ALT-X	30.00	36.00

Ordering Information



			GENERAL TOLERANCE		制图 DRAWING		深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO., LTD			
			DIM	TOL	审核 CHECK					
			X, X	±0.30	批准 APPROVAL		产品名称 TITLE	2.0 立贴	版本 REV.	A
			X, XX	±0.20	比例 SCALE		产品料号 PART NO.	HC-HY-NALT-X	单位 UNITS	mm
			X, XXX	±0.10	投影 Projection		材料 MATERIAL		页次 SHEET	1/1
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE	Angle ±3.0°							