


SPECIFICATIONS

- 1、Current Rating: 1A AC, DC
- 2、Voltage Rating: 125V AC, DC
- 3、Temperatuer Range: -25°C~ +85°C
- 4、Contact Resistance: 20mΩ Max
- 5、Insulation Resistance: 100mΩ Min
- 6、Withstanding Voltang: 500V AC/minute
- 7、Material: Wafer Nylon46 UL94-VO
Pin Brass Tin-plated

Circuit	PA-XXrt NO.	Dimensions mm	
		A	B
2	XD-1.25-2A-XX	1.25	4.25
3	XD-1.25-3A-XX	2.50	5.50
4	XD-1.25-4A-XX	3.75	6.75
5	XD-1.25-5A-XX	5.00	8.00
6	XD-1.25-6A-XX	6.25	9.25
7	XD-1.25-7A-XX	7.50	10.50
8	XD-1.25-8A-XX	8.75	11.75
9	XD-1.25-9A-XX	10.00	13.00
10	XD-1.25-10A-XX	11.25	14.25
11	XD-1.25-11A-XX	12.50	15.50
12	XD-1.25-12A-XX	13.75	16.75
13	XD-1.25-13A-XX	15.00	18.00
14	XD-1.25-14A-XX	16.25	19.25
15	XD-1.25-15A-XX	17.50	20.50
16	XD-1.25-16A-XX	18.75	21.75

Ordering Information



GENERAL TOLERANCE			制图 DRAWING	02	深圳讯答科技有限公司 ShenzhenXuntaTechnology Co.,Ltd			
DIM TOL			审核 CHECK					产品名称 TITLE
X.X ±0.30			批准 APPROVAL		产品料号 PART NO.	XD-1.25-NA-XX	单位 UNITS	mm
X.XX ±0.20			投影 Projection		材料 MATERIAL		页次 SHEET	1/1
X.XXX ±0.10								
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE						
Angle ±3.0°								