


SPECIFICATIONS

- 1、Current Rating: 1A AC, DC
- 2、Voltage Rating: 125V AC, DC
- 3、Temperatuer Range: -25℃~ +85℃
- 4、Contact Resistance: 20mΩ Max
- 5、Insulation Resistance: 100mΩ Min
- 6、Withstanding Voltang: 500V AC/minute
- 7、Material: Wafer Nylon46 UL94-VO
Pin Brass Tin-plated

Circuit	PA-XXrt NO.	Dimensions mm	
		A	B
2	XD-1.25-2AW-XX	1.25	4.25
3	XD-1.25-3AW-XX	2.50	5.50
4	XD-1.25-4AW-XX	3.75	6.75
5	XD-1.25-5AW-XX	5.00	8.00
6	XD-1.25-6AW-XX	6.25	9.25
7	XD-1.25-7AW-XX	7.50	10.50
8	XD-1.25-8AW-XX	8.75	11.75
9	XD-1.25-9AW-XX	10.00	13.00
10	XD-1.25-10AW-XX	11.25	14.25
11	XD-1.25-11AW-XX	12.50	15.50
12	XD-1.25-12AW-XX	13.75	16.75
13	XD-1.25-13AW-XX	15.00	18.00
14	XD-1.25-14AW-XX	16.25	19.25
15	XD-1.25-15AW-XX	17.50	20.50
16	XD-1.25-16AW-XX	18.75	21.75

Ordering Information



			GENERAL TOLERANCE	制图 DRAWING	02	深圳讯答科技有限公司 Shenzhen Xunta Technology Co., Ltd			
			DIM TOL	审核 CHECK					产品名称 TITLE
			X.X ±0.30	批准 APPROVAL		产品料号 PART NO.	XD-1.25-NAW-XX	单位 UNITS	mm
			X.XX ±0.20	比例 SCALE		材料 MATERIAL		页次 SHEET	1/1
			X.XXX ±0.10	投影 Projection					
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE	Angle ±3.0°						