


SPECIFICATIONS

- 1、Current Rating: 1A AC, DC
- 2、Voltage Rating: 125V AC, DC
- 3、Temperatuer Range: -25℃~ +85℃
- 4、Contact Resistance: 20mΩ Max
- 5、Insulation Resistance: 100mΩ Min
- 6、Withstanding Voltang: 500V AC/minute
- 7、Material: Housing Nylon66 UL94-VO

Circuit	Part NO.	Dimensions mm	
		A	B
2	XD-1.25-2Y	1.25	4.25
3	XD-1.25-3Y	2.50	5.50
4	XD-1.25-4Y	3.75	6.75
5	XD-1.25-5Y	5.00	8.00
6	XD-1.25-6Y	6.25	9.25
7	XD-1.25-7Y	7.50	10.50
8	XD-1.25-8Y	8.75	11.75
9	XD-1.25-9Y	10.00	13.00
10	XD-1.25-10Y	11.25	14.25
11	XD-1.25-11Y	12.50	15.50
12	XD-1.25-12Y	13.75	16.75
13	XD-1.25-13Y	15.00	18.00
14	XD-1.25-14Y	16.25	19.25
15	XD-1.25-15Y	17.50	20.50
16	XD-1.25-16Y	18.75	21.75

Ordering Information



GENERAL TOLERANCE			制图 DRAWING	02	深圳讯答科技有限公司 ShenzhenXuntaTechnology Co.,Ltd			
DIM TOL			审核 CHECK					
X.X ±0.30			批准 APPROVAL		产品料号 PART NO.	XD-1.25-NY	单位 UNITS	mm
X.XX ±0.20			投影 Projection		材料 MATERIAL		页次 SHEET	1/1
X.XXX ±0.10								
Angle ±3.0°								
1	初版发行							
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE						