


PROPERTY OF DEUTSCH E.C.D.  
 THIS DRAWING CONTAINS PROPRIETARY INFORMATION THAT SHALL NOT BE DISCLOSED,  
 DUPLICATED, NOR USED IN WHOLE OR IN PART FOR ANY PURPOSE OTHER THAN TO  
 EVALUATE THIS DRAWING.

6462-239/242-12/22xx

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
-	NEW RELEASE PER E.O. D0453	130318	AR



DEUTSCH PART NO.	BOEING PART NO.	COLOR BANDS	SIZE	WIRE GAGE RANGE	RECOMMENDED STRIP LENGTH	CRIMP TOOL		A MIN.	B MIN.	C MAX.
						MS	TOOL POSITIONER			
6462-242-22341 6462-242-2231	BACC47GD1	GREEN	22D	22, 24, 26, 28	.160 TO .190	M22520/2-01 M22520/7-01	M22520/2-07 M22520/7-05	.141	.0335	.048
6462-241-20341 6462-241-2031	BACC47GD2	RED	20	20, 22, 24	.230 TO .260	M22520/1-01 M22520/2-01 M22520/7-01	M22520/1-04 M22520/2-10 M22520/7-08	.209	.046	.070
6462-240-16341 6462-240-1631	BACC47GD3	BLUE	16	16, 18, 20	.230 TO .260	M22520/1-01 M22520/7-01	M22520/1-04 M22520/7-04	.209	.066	.103
6462-239-12341 6462-239-1231	BACC47GD4	YELLOW	12	12 AND 14	.230 TO .260	M22520/1-01	M22520/1-04	.209	.098	.151



PART NUMBER	PLATING SOCKET BODY	PLATING HOOD
6462-242-2231 6462-241-2031 6462-240-1631 6462-239-1231	OVERALL FINISH .000050 MIN. GOLD PER MIL-DTL-45204 OVER NICKEL	PASSIVATED
6462-242-22341 6462-241-20341 6462-240-16341 6462-239-12341	SELECTIVE PLATING PER AS39029 WITH 10 MICROINCHES MIN. THICK GOLD FLASH	PASSIVATED

- MATERIAL: SOCKET BODY - COPPER ALLOY  
SOCKET HOOD - STAINLESS STEEL
- FINISH: SEE TABLE
- DIMENSIONS ARE IN INCHES UNLESS OTHERWISE SPECIFIED.

UNLESS OTHERWISE SPECIFIED: DIMENSIONS ARE IN INCHES DECIMALS XXX ± .005 ANGLES ± 0° 30' 0" T.I.R. .010 PARTS TO HAVE NO BURRS OR SHARP EDGES	SIGNATURE & DATE	
	DR	RAO CHAUDHRI 130315
MATERIAL SEE NOTE 3	CHK	AR 130318
	PE	RAO CHAUDHRI 130315
FINISH SEE NOTE 2	APPD	AR 130318
	SCALE	WT NONE

CONTACT, SOCKET  
 CRIMP TYPE  
 BACC47GD  
 ENVELOPE

CP ---	MATL CODE 64
<b>DEUTSCH</b> ENGINEERED CONNECTING DEVICES 250 EDDIE JONES WAY OCEANSIDE, CA 92058	
<b>A</b> DWG SIZE	6462-239/242-12/22xx
CODE 11139	SHEET   OF

BACC47GD4-ENV