



1

2

3

4

5



Specifications:

Current rating:3.0A AC,DC

Voltage rating:250V AC,DC

Contact resistance:10m ohm max

Insulation resistance:1000M ohm min

Withstanding voltage:800V AC/Minute

Operating Temperature range:-25°C ~ +85°C

Material and Finish:

Material:Nylon 66 (UL94V-0)

Dimension:

Circuits	DIM.A	DIM.B	Circuits	DIM.A	DIM.B
2	2.50	5.70	10	22.50	25.70
3	5.00	8.20	11	25.00	28.20
4	7.50	10.70	12	27.50	30.70
5	10.00	13.20			
6	12.50	15.70			
7	15.00	18.20			
8	17.50	20.70			
9	20.00	23.20			

RoHS Compliant

DRAWN:

GENERAL TOLERANCE:

.X=±0.30

.XX=±0.20

CHECKED:

UNIT: MM

DESCRIPTION:

Wire-To Board Housing,2.5mm,J Series

SIZE

APPROVAL:

SCALE:1:1

SHEET: 1 / 1

PART NO:

51225-XX

A4


REV

DATE

FILE

BY

PROJECTION:



CnC Tech

Industrial Cable and Connector Technology