


SPECIFICATIONS

1. Current Rating: 3A AC, DC
2. Voltage Rating: 250V AC, DC
3. Temperature Range: -25°C~ +85°C
4. Contact Resistance: 20mΩ Max
5. Insulation Resistance: 1000mΩ Min
6. Withstanding Voltage: 800V AC/minute
7. Material: Housing Nylon66 UL94-VO

Circuit	Part NO.	Dimensions mm	
		A	B
2	XD-PHD-2x2Y-X	2.00	6.00
3	XD-PHD-2x3Y-X	4.00	8.00
4	XD-PHD-2x4Y-X	6.00	10.00
5	XD-PHD-2x5Y-X	8.00	12.00
6	XD-PHD-2x6Y-X	10.00	14.00
7	XD-PHD-2x7Y-X	12.00	16.00
8	XD-PHD-2x8Y-X	14.00	18.00
9	XD-PHD-2x9Y-X	16.00	20.00
10	XD-PHD-2x10Y-X	18.00	22.00
11	XD-PHD-2x11Y-X	20.00	24.00
12	XD-PHD-2x12Y-X	22.00	26.00
13	XD-PHD-2x13Y-X	24.00	28.00
14	XD-PHD-2x14Y-X	26.00	30.00
15	XD-PHD-2x15Y-X	28.00	32.00
16	XD-PHD-2x16Y-X	30.00	34.00
17	XD-PHD-2x17Y-X	32.00	36.00
18	XD-PHD-2x18Y-X	34.00	38.00
19	XD-PHD-2x19Y-X	36.00	40.00
20	XD-PHD-2x20Y-X	38.00	42.00

Ordering Information

XD - PHD - N \*\*\* - \*



GENERAL TOLERANCE			制图 DRAWING	02	深圳讯答科技有限公司 ShenzhenXunDaTechnology Co.,Ltd			
DIM TOL			审核 CHECK					
X.X ±0.30			批准 APPROVAL		产品名称 TITLE	PHD (2.00) 双排 孔座	版本 REV.	A
X.XX ±0.20			比例 SCALE		产品料号 PART NO.	XD-PHD-2xNY-X	单位 UNITS	mm
X.XXX ±0.10			投影 Projection		材料 MATERIAL		页次 SHEET	1/1
1	初版发行							
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE						