



SPECIFICATIONS

1. Current Rating: 2A AC, DC
2. Voltage Rating: 250V AC, DC
3. Temperature Range: -25°C~ +85°C
4. Contact Resistance: 20mΩ Max
5. Insulation Resistance: 1000mΩ Min
6. Withstanding Voltage: 1000V AC/minute
7. Material: Wafer LCP UL94-VO
Pin Brass Tin-plated

Circuit	Part NO.	Dimensions mm		
		A	B	C
2	XD-PH-2AWT-XX	2.00	8.00	6.70
3	XD-PH-3AWT-XX	4.00	10.00	8.70
4	XD-PH-4AWT-XX	6.00	12.00	10.70
5	XD-PH-5AWT-XX	8.00	14.00	12.70
6	XD-PH-6AWT-XX	10.00	16.00	14.70
7	XD-PH-7AWT-XX	12.00	18.00	16.70
8	XD-PH-8AWT-XX	14.00	20.00	18.70
9	XD-PH-9AWT-XX	16.00	22.00	20.70
10	XD-PH-10AWT-XX	18.00	24.00	22.70
11	XD-PH-11AWT-XX	20.00	26.00	24.70
12	XD-PH-12AWT-XX	22.00	28.00	26.70
13	XD-PH-13AWT-XX	24.00	30.00	28.70
14	XD-PH-14AWT-XX	26.00	32.00	30.70
15	XD-PH-15AWT-XX	28.00	34.00	32.70
16	XD-PH-16AWT-XX	30.00	36.00	34.70

Ordering Information

XD - PH - N *** - **

Pin Type Contact Plating
 1#无通 2#1.0 Gold
 AW=带针 G22# Gold
 AL=20# G23# Gold
 AW=带针 G44# Gold
 G53# Gold

			GENERAL TOLERANCE	制图 DRAWING	01	深圳讯答科技有限公司 ShenzhenXunDaTechnology Co.,Ltd			
			DIM TOL	审核 CHECK					
			X.X ±0.30	批准 APPROVAL		产品名称 TITLE	PH (2.00) 单排 卧贴	版本 REV.	A
			X.XX ±0.20	比例 SCALE		产品料号 PART NO.	XD-PH-NAWT-XX	单位 UNITS	mm
			X.XXX ±0.10	投影 Projection		材料 MATERIAL		页次 SHEET	1/1
1	初版发行		Angle ±3.0°						
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE							