



SPECIFICATIONS

1. Current Rating: 3A AC, DC
2. Voltage Rating: 250V AC, DC
3. Temperature Range: -25°C~ +85°C
4. Contact Resistance: 10mΩ Max
5. Insulation Resistance: 1000mΩ Min
6. Withstanding Voltage: 1000V AC/minute
7. Material: Wafer PA66 UL94-V0
Pin Brass Tin-plated

Circuit	Part NO.	Dimensions mm		
		A	B	C
2	XD-XHB-2A-X-XX	2.50	7.50	2.50
3	XD-XHB-3A-X-XX	5.00	10.00	3.10
4	XD-XHB-4A-X-XX	7.50	12.50	3.60
5	XD-XHB-5A-X-XX	10.00	15.00	6.10
6	XD-XHB-6A-X-XX	12.50	17.50	8.60
7	XD-XHB-7A-X-XX	15.00	20.00	11.10
8	XD-XHB-8A-X-XX	17.50	22.50	13.60
9	XD-XHB-9A-X-XX	20.00	25.00	16.10
10	XD-XHB-10A-X-XX	22.50	27.50	18.60
11	XD-XHB-11A-X-XX	25.00	30.00	21.10
12	XD-XHB-12A-X-XX	27.50	32.50	23.60
13	XD-XHB-13A-X-XX	30.00	35.00	26.10
14	XD-XHB-14A-X-XX	32.50	37.50	28.60
15	XD-XHB-15A-X-XX	35.00	40.00	31.10
16	XD-XHB-16A-X-XX	37.50	42.50	33.60
17	XD-XHB-17A-X-XX	40.00	45.00	36.10
18	XD-XHB-18A-X-XX	42.50	47.50	38.60
19	XD-XHB-19A-X-XX	45.00	50.50	41.10
20	XD-XHB-20A-X-XX	47.50	52.50	43.60

Ordering Information



		GENERAL TOLERANCE	制图 DRAWING	10	深圳讯答科技有限公司 ShenzhenXunDaTechnology Co.,Ltd			
		DIM TOL	审核 CHECK					
		X.X ±0.30	批准 APPROVAL		产品名称 TITLE	XHB (2.50) 单排带扣 直针	版本 REV.	A
		X.XX ±0.20	比例 SCALE		产品料号 PART NO.	XD-XHB-NA-X-XX	单位 UNITS	mm
		X.XXX ±0.10	投影 Projection		材料 MATERIAL		页次 SHEET	1/1
1	初版发行							
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE						