


SPECIFICATIONS

1. Current Rating: 3A AC, DC
2. Voltage Rating: 250V AC, DC
3. Temperature Range: -25°C~ +85°C
4. Contact Resistance: 30mΩ Max
5. Insulation Resistance: 1000mΩ Min
6. Withstanding Voltage: 650V AC/minute
7. Material: Wafer Nylon66 UL94-VO  
PIN Brass Tin-plated

Circuit	Part NO.	Dimensions mm	
		A	B
2	XD-XHD-2x2A-X-XX	2.50	7.50
3	XD-XHD-2x3A-X-XX	5.00	10.00
4	XD-XHD-2x4A-X-XX	7.50	12.50
5	XD-XHD-2x5A-X-XX	10.00	15.00
6	XD-XHD-2x6A-X-XX	12.50	17.50
7	XD-XHD-2x7A-X-XX	15.00	20.00
8	XD-XHD-2x8A-X-XX	17.50	22.50
9	XD-XHD-2x9A-X-XX	20.00	25.00
10	XD-XHD-2x10A-X-XX	22.50	27.50
11	XD-XHD-2x11A-X-XX	25.00	30.00
12	XD-XHD-2x12A-X-XX	27.50	32.50
13	XD-XHD-2x13A-X-XX	30.00	35.00
14	XD-XHD-2x14A-X-XX	32.50	37.50
15	XD-XHD-2x15A-X-XX	35.00	40.00
16	XD-XHD-2x16A-X-XX	37.50	42.50
17	XD-XHD-2x17A-X-XX	40.00	45.00
18	XD-XHD-2x18A-X-XX	42.50	47.50
19	XD-XHD-2x19A-X-XX	45.00	50.00
20	XD-XHD-2x20A-X-XX	47.50	52.50

Ordering Information



GENERAL TOLERANCE			制图 DRAWING	05	深圳讯答科技有限公司 ShenzhenXunDaTechnology Co.,Ltd			
DIM TOL			审核 CHECK					
X.X ±0.30			批准 APPROVAL		产品名称 TITLE	XHD (2.50) 双排 直针	版本 REV.	A
X.XX ±0.20			比例 SCALE		产品料号 PART NO.	XD-XHD-2xNA-X-XX	单位 UNITS	mm
X.XXX ±0.10			投影 Projection		材料 MATERIAL		页次 SHEET	1/1
1	初版发行		角度 Angle	±3.0°				
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE						