


REV. 1 1/27/92

COIL: @ +25 °C	
RESISTANCE	600 OHMS
NOMINAL VOLTAGE	26.5 VDC
MUST OPERATE	13.4 VDC
MUST RELEASE	1.5 VDC

ENVIRONMENT:	
VIBRATION	10 CPS TO 2000 CPS @ 20 g's
SHOCK	100 g's 6 MS. DURATION
TEMPERATURE	-65 °C TO +125 °C

NOTES: OPERATE TIME 4 MS MAX.  
 RELEASE TIME 3 MS MAX.  
 CONTACT BOUNCE 3 MS MAX.

CUSTOMER DATA SHEET



CONTACT RATING: 4 AMPS  
 30 VDC RESISTIVE 100,000 OPERATIONS

DR. R.B. 12/11/91 CK1/2710

COMMUNICATIONS  
 INSTRUMENTS, INC.

CUST. Hi-G  
 CUST. NO. 2HA-1C-126

TYPE HFW4A RELAY

HFW4A1140S01